



PHILIPS
RESPIRONICS

DreamStation

Auto CPAP

DreamStation helps support long-term patient use while creating **new efficiencies for your business.**

Connectivity options offer more monitoring choices than any leading CPAP brand with integrated Bluetooth® on every device, and offering optional Wi-Fi and cellular modems.*

Performance Check simplifies in-home device evaluation and can help reduce the number of normally functioning devices that are returned for service.

EZ-Start's automatic, personalized adjustments to CPAP pressure can help patients gradually acclimate to their prescribed level of therapy.

Daily Progress Feedback displays a simple trend of patients' nightly use to help track progress on the path to adherence.

DreamStation features

- Advanced event detection
- Mask type resistance control
- Mask fit check
- Oximetry capable
- Encore patient management system with optional Adherence Profiler
- DreamMapper patient self-management system compatibility

Humidification

- Fixed, adaptive, heated tube
- Pre-heat humidifier option
- Modular design with one-piece, dishwasher-safe water chamber

Protection programs

- Flex Promise program
- Bi-level Rescue program
- "One-Touch" warranty programs

Auto CPAP features

- C-Flex, C-Flex+, A-Flex
- SmartRamp
- EZ-Start
- CPAP-Check
- Auto-Trial
- Opti-Start
- Digital AutoTrak
- Advanced event detection
- Waveform data
- Standard integrated Bluetooth

*Internal assessment of 2015 competitive CPAP data comparing to ResMed Aironse10/Aircurve10 platform and Fisher & Paykel Icon series platform.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and the use of such marks by Philips Respironics is under license. Other trademarks and trade names are those of their respective owners.

DreamStation Auto CPAP

Comfort features			Encore data capture and reporting	
Modes	Features	Flex Comfort	Advanced Event Detection	Flow Waveforms
Fixed CPAP CPAP-Check Auto-CPAP	EZ-Start Auto-Trial Opti-Start	C-Flex C-Flex+ A-Flex	Standard	Standard

Specifications

DreamStation Auto CPAP

Pressure range	4 to 20 cm H2O
Flex pressure relief	0 to 3
Ramp time	0 to 45 min (5-minute increments)
Starting ramp pressure	4 cm H2O to CPAP Pressure (CPAP); 4cm H2O to Min Pressure (Auto CPAP)
Humidification	Heated humidification: Fixed, Adaptive, Heated Tube modes; Heated Tube (optional)
Data storage capacity (minimum)	SD card: > 1 year On-board: <6 months
Altitude compensation	Automatic
Filters	Reusable pollen; disposable ultra-fine
Device controls	LCD, control dial/push button
Warranty	2 years (US)
Dimensions	15.7x19.3x8.4cm (w/o humidifier) 29.7x19.3x8.4cm (w/ humidifier)
Weight	1.33kg/2.94lbs (w/o humidifier) 1.98kg/4.37lbs (w/humidifier) Incl. power supply
Electrical requirements	100 – 240 VAC, 50/60 Hz, 2.0-1.0 A

Ordering information

Humidification	Part number
DreamStation Humidifier, India	IAXH
DS Humid, User Manual, EN-INTL NON-CE v00	1154354

Ordering information

DreamStation Auto CPAP	Part number
DreamStation Auto CPAP, India W/C7 END, INDIA	IAX500S15
POWER CORD W/C7 END, INDIA	1060017
DS CPAP, User Manual, EN-INTL NON-CE v00	1154355
DS Provider Guide, EN-INTL NON-CE v00	1154357

© 2015 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
(Royal Philips) or their respective owners.

www.philips.com



Caution: US federal law restricts these devices to sale by or on the order of a physician.

edoc EB 11/12/15 MCI 4107067
1010 Murry Ridge Lane, Murrysville, PA 15668
800-345-6443 • 724-387-4000